

# Product data sheet

Specifications



## OptiLine 45 OptiLine 70 - ceiling fixing - white

ISM20814

⚠ Discontinued on: Jun 30, 2023

⚠ Discontinued

### Main

Cabling Installation System	Pole
Product Or Component Type	Ceiling fixing

### Complementary

Type Of Pole	One-sided Two-sided
Colour Tint	White (RAL 9010)
Quantity Per Set	Set of 1
Pole/Post Surface Finish	Powder coated Anodized
Pole Fixing Mode	Tension-mounted
Fixing Mode	By screws
Material	Aluminium powder coated
Length	120 mm
Height	75 mm
Width	50 mm
Market Segment	Residential Small commercial

### Environment

Ambient Air Temperature For Operation	-25...60 °C
Ip Degree Of Protection	IP30

### Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	12 cm
Package 1 Width	5 cm
Package 1 Length	7.5 cm
Package 1 Weight	355 g
Unit Type Of Package 2	CAR
Number Of Units In Package 2	30

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 2 Height	39.8 cm
Package 2 Width	30 cm
Package 2 Length	29.9 cm
Package 2 Weight	11.44 kg
Unit Type Of Package 3	PAL
Number Of Units In Package 3	240
Package 3 Height	75 cm
Package 3 Width	80 cm
Package 3 Length	120 cm
Package 3 Weight	111.52 kg

## Contractual warranty

Warranty	18 months
----------	-----------

## Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency

## Well-being performance

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information [Yes](#)

<b>Eu Rohs Directive</b>	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
--------------------------	---

<b>China Rohs Regulation</b>	<a href="#">China RoHS declaration</a> Pro-active China RoHS declaration (out of China RoHS legal scope)
------------------------------	---

<b>Environmental Disclosure</b>	<a href="#">Product Environmental Profile</a>
---------------------------------	---

<b>Circularity Profile</b>	No need of specific recycling operations
----------------------------	--