

Product data sheet

Specifications

OptiLine 45 - mounting frame

ISM50806



⚠ Discontinued on: Jun 30, 2023

⚠ Discontinued

Main

Range	OptiLine
Cabling Installation System	Floor box
Product Type	Mounting frame
Type Of Floor	In-cavity floor Screeded floor Raised floor
Floor Box Shape	Rectangular
Colour	Light grey
Quantity Package 1 / Unit	4 pieces

Complementary

Suitable For	For 2-4 Unica outlets
Fixing Mode	Snap-fitted
Number Of Modules	4 modules
Product Material	PBT (polybutylene terephthalate)
Length	216 mm
Height	38 mm
Width	64 mm

Environment

Operating Temperature	-25...60 °C
Ip Degree Of Protection	IP20

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	4.0 cm
Package 1 Width	6.5 cm
Package 1 Length	21.5 cm
Package 1 Weight	65.0 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	4

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 2 Height	15.5 cm
Package 2 Width	6.5 cm
Package 2 Length	21.5 cm
Package 2 Weight	273.0 g
Unit Type Of Package 3	S03
Number Of Units In Package 3	40
Package 3 Height	30.0 cm
Package 3 Width	30.0 cm
Package 3 Length	40.0 cm
Package 3 Weight	3.217 kg

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency

Well-being performance

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information [Yes](#)

Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
--------------------------	---

China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
------------------------------	---

Environmental Disclosure	Product Environmental Profile
---------------------------------	---

Circularity Profile	No need of specific recycling operations
----------------------------	--