

# Product data sheet

Specifications



## OptiLine 70 - adaptor - 1 module

ISM15205

⚠ Discontinued on: Jul 19, 2021

⚠ Discontinued

### Main

Range Of Product	OptiLine 70
Cabling Installation System	Trunking Pole
Product Type	Adaptor
Trunking Material	Plastic Aluminium
Type Of Pole	Two-sided One-sided
Trunking Dimension	80 x 55 mm 120 x 55 mm 95 x 55 mm 185 x 55 mm 155 x 55 mm
Suitable For	Unica wiring device
Pole/Post Surface Finish	Anodized
Pole Fixing Mode	Free-standing Tension-mounted

### Complementary

Number Of Modules	1 module
Colour	Aluminium metallic
Fixing Mode	Snap-fitted
Product Material	PC/ABS painted
Quantity Package 1 / Unit	Set of 1
Length	71 mm
Height	73 mm
Width	28 mm

### Environment

Standards	73/23/EEC 93/68/EEC EN 50085-1:2005 EN 50085-2-1:2002
Operating Temperature	-25...60 °C
Ip Degree Of Protection	IP21

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

## Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	2.8 cm
Package 1 Width	7.3 cm
Package 1 Length	7.1 cm
Package 1 Weight	29.8 g

## Contractual warranty

Warranty	18 months
----------	-----------

## Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency   RoHS/REACH

## Well-being performance

✓ Reach Free Of Svhc

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information   Yes

## Certifications & Standards

Reach Regulation	<a href="#">REACH Declaration</a>
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
China Rohs Regulation	<a href="#">China RoHS declaration</a> Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations