

Product data sheet

Specifications



OptiLine 45 - pole - tension-mounted - two-sided - natural - 3500-3900 mm

ISM20110

Main

| | |
|-----------------------------|------------------------------|
| Range | OptiLine |
| Product Name | OptiLine 45 |
| Shape | Oval |
| Cabling Installation System | Pole |
| Product Type | Pole |
| Device Presentation | Empty |
| Type Of Pole | Two-sided |
| Pole/Post Surface Finish | Anodized |
| Pole Fixing Mode | Tension-mounted |
| Adjustment | Adjustable in height: 400 mm |

Complementary

| | |
|---------------------------|--|
| Additional Information | Adjustability of ceiling fixing 400 mm |
| Colour | Natural |
| Front Opening Size | 45 mm |
| Material | Aluminium anodized |
| Quantity Package 1 / Unit | Set of 1 |
| Height | 3500...3900 mm |
| Depth | 90 mm |
| Width | 116 mm |
| Cover Type | 2 closed cover cover 45 mm in aluminium anodized |
| Useful Cross Section | 696 mm² |
| Compartment Partitioning | 2 compartments |

Environment

| | |
|-------------------------|--|
| Standards | 73/23/EEC 93/68/EEC EN 50085-1:2005 EN 60598-2-2 IEC 1084-2-4 NF C 68-102 SS 424 10 32 |
| Operating Temperature | -25...60 °C |
| Ip Degree Of Protection | IP30 |

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Packing Units

| | |
|------------------------------|------------|
| Unit Type Of Package 1 | PCE |
| Number Of Units In Package 1 | 1 |
| Package 1 Height | 12.500 cm |
| Package 1 Width | 16.000 cm |
| Package 1 Length | 366.500 cm |
| Package 1 Weight | 12.000 kg |
| Unit Type Of Package 2 | PAL |
| Number Of Units In Package 2 | 28 |
| Package 2 Height | 69.000 cm |
| Package 2 Width | 120.000 cm |
| Package 2 Length | 370.000 cm |
| Package 2 Weight | 366.000 kg |

Contractual warranty

| | |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency RoHS/REACH

Well-being performance

✓ Reach Free Of Svhc

✓ Rohs Exemption Information [Yes](#)

Certifications & Standards

| | |
|--------------------------|---|
| Reach Regulation | REACH Declaration |
| Eu Rohs Directive | Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration |
| China Rohs Regulation | China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope) |
| Environmental Disclosure | Product Environmental Profile |
| Circularity Profile | No need of specific recycling operations |