

# Product data sheet

Specifications



## OptiLine 70 - pole - free-standing - two-sided - natural - 2420 mm

ISM20521

### Main

Range	OptiLine
Product Name	OptiLine 70
Cabling Installation System	Pole
Product Type	Pole
Type Of Pole	Two-sided
Pole/Post Surface Finish	Anodized
Pole Fixing Mode	Free-standing

### Complementary

Colour	Natural
Front Opening Size	70 mm
Material	Aluminium anodized
Quantity Package 1 / Unit	Set of 1
Height	2420 mm
Depth	118 mm
Width	120 mm

### Environment

Standards	73/23/EEC 93/68/EEC IEC 1084-2-4 SS 424 10 32 EN-AW-6063
Operating Temperature	-25...60 °C
Ip Degree Of Protection	IP40

### Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	11.8 cm
Package 1 Width	12.0 cm
Package 1 Length	242.0 cm
Package 1 Weight	9.596 kg
Unit Type Of Package 2	PAL

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Number Of Units In Package 2	16
Package 2 Height	92.0 cm
Package 2 Width	255.0 cm
Package 2 Length	120.0 cm
Package 2 Weight	173.536 kg

## Contractual warranty

Warranty	18 months
----------	-----------

## Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency   RoHS/REACH

## Well-being performance

✓ Reach Free Of Svhc

✓ Rohs Exemption Information   [Yes](#)

## Certifications & Standards

Reach Regulation	<a href="#">REACH Declaration</a>
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
China Rohs Regulation	<a href="#">China RoHS declaration</a> Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations