


# Product data sheet

Specifications



## Earth-leakage add-on protection module, ComPact NSX 400/630, MB type, 200 to 440 VAC, 300 mA to 30 A, 4P

LV432456

❗ Discontinued

❗ Discontinued on: Feb 7, 2022

### Main

Range Of Product	ComPact NSX400...630
Range	ComPact
Product Or Component Type	Vigi add-on
Device Application	Wiring
Range Compatibility	ComPact ComPact NSX400 circuit breaker ComPact ComPact NSX630 circuit breaker EasyPact EasyPact CVS400 circuit breaker EasyPact EasyPact CVS630 circuit breaker
Poles Description	4P
[In] Rated Current	400 A 630 A
Earth-Leakage Add-On Module Name	MB
Earth-Leakage Protection Class	Class A
Residual Earth-Leakage Sensitivity Adjustment Type	Adjustable 5 settings
Earth-Leakage Sensitivity	0.3 A 1 A 3 A 10 A 30 A
Residual Earth-Leakage Time Delay Adjustment Type	Adjustable 4 settings
[Δt] Residual Earth-Leakage Time Delay Adjustment	150 ms 0 ms 310 ms 60 ms

### Complementary

Network Type	AC
Network Frequency	50/60 Hz
[Ue] Rated Operational Voltage	200...440 V AC 50/60 Hz conforming to IEC 60947-2
Earth-Leakage Protection	With
Maximum Breaking Time	800 ms
Overvoltage Category	Class II

### Environment

Electrical Shock Protection Class	Class II
-----------------------------------	----------

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Standards	IEC 60947-2
-----------	-------------

## Contractual warranty

Warranty	18 months
----------	-----------

## Sustainability

**Green Premium™** label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency   RoHS/REACH

## Well-being performance

✓ Mercury Free

✓ Rohs Exemption Information   [Yes](#)

✓ Pvc Free

## Certifications & Standards

Reach Regulation	<a href="#">REACH Declaration</a>
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	<a href="#">China RoHS declaration</a> Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	<a href="#">End of Life Information</a>
California Proposition 65	WARNING: Cancer and Reproductive Harm - <a href="#">www.P65Warnings.ca.gov</a>