

Product data sheet

Specifications



APC Line-R 1550VA Automatic Voltage Regulator, 3 Schuko Outlets, 230V Russia

LN1550-RS

 To be discontinued on: Apr 30, 2024

 To be discontinued

Overview

Lead Time Usually in Stock

Main

Main Input Voltage	230 V
Main Output Voltage	230 V
Rated Power In W	750 W
Rated Power In Va	1550 VA
Input Connection Type	Schuko CEE 7/7P
Cable Length	1.00 m
Provided Equipment	User manual

Batteries & Runtime

Number Of Battery Filled Slots	0
Number Of Battery Free Slots	0

Physical

Colour	Black
Height	11.9 cm
Width	9.5 cm
Depth	18 cm
Net Weight	1.96 kg
Mounting Preference	No preference
Mounting Mode	Not rack-mountable
Two Post Mountable	0
Usb Compatible	No

Input

Network Frequency	50 Hz
Input Voltage Limits	184...284 V

Output

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Maximum Configurable Power In W	750 W
---------------------------------	-------

Conformance

Product Certifications	EAC
------------------------	-----

Environmental

Ambient Air Temperature For Operation	0...40 °C
Relative Humidity	0...90 %
Operating Altitude	0...3333 ft
Ambient Air Temperature For Storage	-20...50 °C
Storage Relative Humidity	0...90 %
Storage Altitude	0.00...1015.90 m

Surge Protection and Filtering

Surge Energy Rate	148 J
-------------------	-------

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	22.8 cm
Package 1 Width	12.5 cm
Package 1 Length	9.8 cm
Package 1 Weight	1.96 kg
Sccl4	10731304340840

Contractual warranty

Warranty	2 years repair or replace
----------	---------------------------

Sustainability



Green Premium™ label is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)

Well-being performance

	Reach Free Of Svhc	
	Mercury Free	
	Rohs Exemption Information	Yes
Reach Regulation		REACH Declaration
Eu Rohs Directive		Compliant EU RoHS Declaration
China Rohs Regulation		China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)