

# Product data sheet

Specifications



Unica - 1 complete RJ45 socket (S-One) - 2 m - Cat.5e, UTP - white/white

MGU10.411.18D

 **Discontinued on:** Jun 15, 2023

 **Discontinued**

## Main

Range	Unica
Aesthetic Name	Unica (standard aesthetic)
Product Or Component Type	Data socket
Device Presentation	Complete product
Colour Tint	White (RAL 9003)
Data Socket Type	RJ45 8 contact(s) Cat.5e < 155 MHz
Provided Equipment	Label holder Protective flap

## Complementary

Communication Network Type	1000BASE-T
Communication Port Protocol	ATM 155 Mbps
Number Of Modules	2 modules
Socket Number	1
Type Of Footprint	Infraplus
Connector Type	S-One
Cable Shielding Type	U/UTP
Organization Of Wire	Unshielded twisted pair
Connections - Terminals	Click
Fixing Mode	Long claws
Installation Direction	Straight
Material	ASA + PC: cover frame ASA + PC: mechanism cover PBT (polybutylene terephthalate) GF30: fixing frame
Depth	36 mm
Embedding Depth	25 mm

## Environment

Ip Degree Of Protection	IP40
Ik Degree Of Protection	IK01
Ambient Air Temperature For Operation	15...30 °C
Ambient Air Temperature For Storage	0...35 °C

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Environmental Characteristic	Alcohol Petrol UV resistant Oil Bleach Liquid soap Window-cleaning fluid Acetone
Standards	ISO 8877

## Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	8 cm
Package 1 Width	8.5 cm
Package 1 Length	4 cm
Package 1 Weight	52 g
Unit Type Of Package 2	CAR
Number Of Units In Package 2	10
Package 2 Height	12 cm
Package 2 Width	17.5 cm
Package 2 Length	26 cm
Package 2 Weight	671 g

## Contractual warranty

Warranty	18 months
----------	-----------

## Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

## Well-being performance

 Reach Free Of Svhc	
 Toxic Heavy Metal Free	
 Mercury Free	
 Rohs Exemption Information	<a href="#">Yes</a>
<b>Reach Regulation</b>	<a href="#">REACH Declaration</a>
<b>Eu Rohs Directive</b>	Compliant <a href="#">EU RoHS Declaration</a>
<b>China Rohs Regulation</b>	<a href="#">China RoHS declaration</a> Pro-active China RoHS declaration (out of China RoHS legal scope)
<b>Weee</b>	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins