

Product data sheet

Specifications



Shunt trip release MX, ComPacT NSX, 220/240VAC 50/60Hz, 208/277VAC 60Hz, screwless spring terminal connections

LV429387

Main

Range	ComPacT
Range of product	ComPacT NSX100...250 ComPacT NSX100...250 new generation ComPacT NSX400...630 ComPacT NSX400...630 new generation ComPacT NSX100...250 DC ComPacT NSX100...250 DC new generation ComPacT NSX100...250 DC PV ComPacT NSX100...250 DC PV new generation ComPacT NSX400...630 DC ComPacT NSX400...630 DC new generation ComPacT NSX400...630 DC PV ComPacT NSX400...630 DC PV new generation
Device short name	MX
Product or component type	Voltage release
Device application	Control
Voltage release type	Opening coil Shunt trip release
[Uc] control circuit voltage	220...240 V AC 50/60 Hz 208...277 V AC 60 Hz
Range compatibility	ComPacT new generation (ComPacT NSX new generation) ComPacT new generation (ComPacT NSX DC new generation) ComPacT (ComPacT NSX) ComPacT (ComPacT NSX DC) EasyPact (EasyPact CVS) PowerPact (PowerPact Multistandard)

Complementary

Operating threshold	0.7...1.1 x Un opening
Response time	50 ms
Control signal type	Impulse Maintained
Impulse duration	>= 20 ms
Supply inrush power	10 VA
Auxiliary connection terminal	Spring 0.5...1.5 mm ² (AWG 20...AWG 16)
Wire stripping length	7 mm

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1

Package 1 Height	4.400 cm
Package 1 Width	4.700 cm
Package 1 Length	6.200 cm
Package 1 Weight	120 g
Unit Type of Package 2	BB1
Number of Units in Package 2	10
Package 2 Height	7.200 cm
Package 2 Width	10.500 cm
Package 2 Length	23.700 cm
Package 2 Weight	1.248 kg
Unit Type of Package 3	S03
Number of Units in Package 3	60
Package 3 Height	30.000 cm
Package 3 Width	30.000 cm
Package 3 Length	40.000 cm
Package 3 Weight	7.844 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
China RoHS Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
PVC free	Yes
California proposition 65	WARNING: This product can expose you to chemicals including: DINP, which is known to the State of California to cause cancer, and DIDP, which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov

Contractual warranty

Warranty	18 months
----------	-----------

Recommended replacement(s)