

Product data sheet

Specifications



Unica - 1 RJ45 socket (S-One) - 1 m - Cat.5e, UTP - ivory

MGU3.410.25

⚠ Discontinued on: Sep 30, 2023

⚠ Discontinued

Main

Range	Unica
Aesthetic Name	Unica (standard aesthetic)
Product Or Component Type	Data socket
Device Presentation	Mechanism
Colour Tint	Ivory (RAL 9010)
Data Socket Type	RJ45 8 contact(s) Cat.5e < 155 MHz
Provided Equipment	Label holder Protective flap

Complementary

Communication Network Type	1000BASE-T
Communication Port Protocol	ATM 155 Mbps
Number Of Modules	1 module
Socket Number	1
Type Of Footprint	Infraplus
Connector Type	S-One
Cable Shielding Type	U/UTP
Organization Of Wire	Unshielded twisted pair
Connections - Terminals	Click
Fixing Mode	Clip-in
Installation Direction	Straight
Material	ASA + PC: mechanism cover
Depth	36 mm
Width	22.5 mm
Height	45 mm
Embedding Depth	25 mm

Environment

Ip Degree Of Protection	IP40
Ik Degree Of Protection	IK01
Ambient Air Temperature For Operation	15...30 °C

Ambient Air Temperature For Storage	0...35 °C
Environmental Characteristic	UV resistant Oil Alcohol Liquid soap Acetone Bleach Petrol Window-cleaning fluid
Standards	ISO 8877

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	2.5 cm
Package 1 Width	4 cm
Package 1 Length	4.5 cm
Package 1 Weight	19 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	10
Package 2 Height	5.5 cm
Package 2 Width	11 cm
Package 2 Length	24.5 cm
Package 2 Weight	247.8 g
Unit Type Of Package 3	S03
Number Of Units In Package 3	170
Package 3 Height	30 cm
Package 3 Width	30 cm
Package 3 Length	40 cm
Package 3 Weight	4.573 kg

Contractual warranty

Warranty	18 months
-----------------	-----------

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

Well-being performance

 Toxic Heavy Metal Free

 Mercury Free

 Rohs Exemption Information Yes

Eu Rohs Directive Compliant
[EU RoHS Declaration](#)

China Rohs Regulation [China RoHS declaration](#)
Pro-active China RoHS declaration (out of China RoHS legal scope)

Weee The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

Circularity Profile No need of specific recycling operations
