

Product data sheet

Specifications



Unica - HDMI data connector type A - 1 module - graphite

MGU3.430.12

⚠ Discontinued on: Sep 30, 2023

⚠ Discontinued

Main

Range	Unica
Product Or Component Type	Audio/video socket
Connector Type	HDMI
Electrical Circuit Type	Audio/video
Device Presentation	Mechanism
Colour Tint	Graphite
Type Of Packing	Group

Complementary

Device Mounting	Flush
Socket Number	1
Fixing Mode	Clip-in
Number Of Modules	1 module
Surface Finish	Matt
Quantity Per Set	Set of 10
Material	Thermoplastic ABS-UV stabilised: centre plate
Height	45 mm
Width	22.5 mm
Depth	41.7 mm
Embedding Depth	25.7 mm
Net Weight	0.01 kg

Environment

Ambient Air Temperature For Storage	-5...50 °C
Ambient Air Temperature For Operation	-5...40 °C
Standards	EN 50049 EN 50157
Ip Degree Of Protection	IP21
Ik Degree Of Protection	IK04

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Environmental Characteristic	Window-cleaning fluid
	Alcohol
	Acetone
	Liquid soap
	Petrol
	Oil
	Bleach
	UV resistant

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	2.5 cm
Package 1 Width	11.0 cm
Package 1 Length	12.0 cm
Package 1 Weight	43.0 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	10
Package 2 Height	8.2 cm
Package 2 Width	20.0 cm
Package 2 Length	22.5 cm
Package 2 Weight	543.0 g
Unit Type Of Package 3	S03
Number Of Units In Package 3	50
Package 3 Height	30.0 cm
Package 3 Width	30.0 cm
Package 3 Length	40.0 cm
Package 3 Weight	3.18 kg

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



RoHS/REACH

Well-being performance

✓ Reach Free Of Svhc

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information Yes

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	No need of specific recycling operations