

Product data sheet

Specifications



Unica Top/Class - TV coaxial cable - 1 m - aluminium

MGU3.468.30

⚠ Discontinued on: Dec 31, 2023

⚠ Discontinued

Main

Range	Unica
Aesthetic Name	Unica Top - Unica Class
Product Or Component Type	TV coaxial cable
Device Application	Connection
Device Presentation	Mechanism
Colour Tint	Aluminium

Complementary

Tv Connector	F connectors
Number Of Modules	1 module
Material	ASA + PC: mechanism cover
Fixing Mode	Clip-in
Depth	28 mm
Width	45 mm
Height	45 mm
Embedding Depth	18 mm
Net Weight	0.09 kg
Ambient Air Temperature For Operation	15...35 °C
Ambient Air Temperature For Storage	0...35 °C
Standards	EN 50083-4 EN 50083-1 EN 50083-2

Environment

Ik Degree Of Protection	IK01
Ip Degree Of Protection	IP20
Environmental Characteristic	Alcohol Bleach Window-cleaning fluid Liquid soap Acetone Petrol Oil UV resistant

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	4.5 cm
Package 1 Width	6.6 cm
Package 1 Length	6.6 cm
Package 1 Weight	13.0 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	10
Package 2 Height	4.6 cm
Package 2 Width	13.5 cm
Package 2 Length	33.2 cm
Package 2 Weight	193.0 g
Unit Type Of Package 3	S01
Number Of Units In Package 3	20
Package 3 Height	15.0 cm
Package 3 Width	15.0 cm
Package 3 Length	40.0 cm
Package 3 Weight	595.0 g

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency RoHS/REACH

Well-being performance

✓	Reach Free Of Svhc	
✓	Toxic Heavy Metal Free	
✓	Mercury Free	
✓	Rohs Exemption Information	Yes

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	No need of specific recycling operations