

# Product data sheet

Specifications



## Unica Allegro - cover frame - 2 modules - light grey

MGU4.102.24

 **Discontinued on:** Jun 15, 2023

 **Discontinued**

### Main

Range	Unica
Device Application	Mounting
Product Or Component Type	Cover frame
Aesthetic Name	Unica Allegro
Number Of Modules	2 modules
Fixing Mode	Clip-in
Cover Frame Colour Tint	Light grey

### Complementary

Material	ABS (acrylonitrile butadiene-styrene): cover frame
Standards	EN 60669-1
Height	80 mm
Width	116 mm
Depth	14 mm
Net Weight	0.018 kg
Market Segment	Small commercial Residential

### Environment

Ik Degree Of Protection	IK01
Ip Degree Of Protection	IP20
Environmental Characteristic	Window-cleaning fluid Petrol Bleach Oil Liquid soap UV resistant Acetone Alcohol

### Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	7 cm
Package 1 Width	9 cm

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 1 Length	3.1 cm
Package 1 Weight	21 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	10
Package 2 Height	7 cm
Package 2 Width	9 cm
Package 2 Length	31 cm
Package 2 Weight	210 kg
Unit Type Of Package 3	S02
Number Of Units In Package 3	30
Package 3 Height	15 cm
Package 3 Width	30 cm
Package 3 Length	40 cm
Package 3 Weight	1085 kg

## Contractual warranty

Warranty	18 months
----------	-----------

## Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency   RoHS/REACH

## Well-being performance



Mercury Free



RoHS Exemption Information

Yes

## Certifications & Standards

Reach Regulation

[REACH Declaration](#)

Eu RoHS Directive

Pro-active compliance (Product out of EU RoHS legal scope)

China RoHS Regulation

[China RoHS declaration](#)

Product out of China RoHS scope. Substance declaration for your information

Environmental Disclosure

[Product Environmental Profile](#)

Circularity Profile

No need of specific recycling operations