

Product data sheet

Specifications



Unica - blind cover plate for - 2 m - ivory

MGU5.866.25ZD

 **Discontinued on:** Jun 15, 2023

 **Discontinued**

Main

Range	Unica
Accessory / Separate Part Category	Fixing accessory
Product Or Component Type	Blind cover
Aesthetic Name	Unica (standard aesthetic)
Number Of Modules	2 modules
Device Presentation	Cover plate with fixing frame
Fixing Mode	Screws
Colour Tint	Cream (RAL 9010)

Complementary

Surface Finish	Untreated
Material	ASA + PC: cover plate Zamak: fixing frame
Standards	EN 60669-1
Depth	14 mm
Width	70.9 mm
Height	70.9 mm
Net Weight	0.0412 kg

Environment

Ik Degree Of Protection	IK01
Ip Degree Of Protection	IP20
Environmental Characteristic	Petrol Bleach Alcohol UV resistant Oil Acetone Window-cleaning fluid Liquid soap

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	1.5 cm

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 1 Width	7.5 cm
Package 1 Length	7.5 cm
Package 1 Weight	42.0 g
Unit Type Of Package 2	CAR
Number Of Units In Package 2	10
Package 2 Height	7.5 cm
Package 2 Width	19.5 cm
Package 2 Length	21.5 cm
Package 2 Weight	420.0 g

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency RoHS/REACH

Well-being performance



Mercury Free



RoHS Exemption Information

Yes

Certifications & Standards

Reach Regulation

[REACH Declaration](#)

Eu RoHS Directive

Pro-active compliance (Product out of EU RoHS legal scope)

China RoHS Regulation

[China RoHS declaration](#)

Product out of China RoHS scope. Substance declaration for your information

Environmental Disclosure

[Product Environmental Profile](#)

Circularity Profile

No need of specific recycling operations