

Product data sheet

Specifications



Unica Class - cover frame - 1 gang - white glass

MGU68.002.7C2

 **Discontinued on:** Sep 30, 2023

 **Discontinued**

Main

Range	Unica
Device Application	Mounting
Product Or Component Type	Cover frame
Aesthetic Name	Unica Class
Number Of Gangs	1 gang
Fixing Mode	Clip-in
Cover Frame Colour Tint	White glass White

Complementary

Material	ASA + PC: decorative frame Glass: cover frame
Standards	EN 60669-1
Height	93 mm
Width	102 mm
Depth	11 mm
Distance Between Centers	71 mm
Net Weight	0.097 kg
Market Segment	Residential Small commercial

Environment

Ik Degree Of Protection	IK01
Ip Degree Of Protection	IP20
Environmental Characteristic	Window-cleaning fluid Alcohol Liquid soap Acetone Petrol UV resistant Oil Bleach

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 1 Height	3.5 cm
Package 1 Width	11.5 cm
Package 1 Length	13.5 cm
Package 1 Weight	132 g
Unit Type Of Package 2	S03
Number Of Units In Package 2	40
Package 2 Height	30 cm
Package 2 Width	30 cm
Package 2 Length	40 cm
Package 2 Weight	5.768 kg
Unit Type Of Package 3	P06
Number Of Units In Package 3	320
Package 3 Height	77 cm
Package 3 Width	80 cm
Package 3 Length	60 cm
Package 3 Weight	55.276 kg

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency RoHS/REACH

Well-being performance

✓ Mercury Free

✓ Rohs Exemption Information [Yes](#)

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations