

# Product data sheet

Specifications



## Unica - replacement lamp - 250 V AC - orange - LED lamp

MGU0.825.AL

⚠ Discontinued on: Feb 21, 2024

⚠ Discontinued

### Main

Range	Unica
Accessory / Separate Part Category	Replacement accessories
Product Or Component Type	Replacement LED
Aesthetic Name	Unica
Light Block Colour	Orange
Bulb Type	LED

### Complementary

[Ue] Rated Operational Voltage	127/230 V AC for switch
Current Consumption	0.15 mA
Temperature Rise	Max +15 °C above ambient temperature
Ambient Air Temperature For Operation	-20...40 °C
Net Weight	0.0034 kg

### Environment

Standards	UNE 60669-1
-----------	-------------

### Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	1.2 cm
Package 1 Width	3.5 cm
Package 1 Length	10.0 cm
Package 1 Weight	4.0 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	10
Package 2 Height	6.2 cm
Package 2 Width	8.0 cm
Package 2 Length	8.5 cm
Package 2 Weight	65.0 g
Unit Type Of Package 3	S01

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Number Of Units In Package 3	90
Package 3 Height	15.0 cm
Package 3 Width	15.0 cm
Package 3 Length	40.0 cm
Package 3 Weight	810.0 g

## Contractual warranty

Warranty	18 months
----------	-----------

## Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency   RoHS/REACH

## Well-being performance

✓ Mercury Free

✓ Rohs Exemption Information   [Yes](#)

## Certifications & Standards

Reach Regulation	<a href="#">REACH Declaration</a>
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	<a href="#">China RoHS declaration</a> Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	No need of specific recycling operations