

Product data sheet

Specifications



Unica - R-TV/SAT socket - individual socket - white

MGU3.454.18

⚠ Discontinued on: Sep 30, 2023

⚠ Discontinued

Main

Range	Unica
Aesthetic Name	Unica (standard aesthetic)
Product Or Component Type	R-TV/SAT socket
Device Presentation	Mechanism
Tv Socket Type	Individual
Colour Tint	White
Condition Of Use	Parallel distribution systems

Complementary

Tv Connector	Male IEC 9.52 mm
Sat Connector	Female IEC 9.52 mm
Path Attenuation	0.8 dB R signal10...108 MHz 0.8 dB TV/UHF signal470...830 MHz 0.8 dB TV/VHF signal118...470 MHz 1.4 dB SAT signal950...2400 MHz
Dc Current Flow	In SAT socket
Number Per Line	1
Number Of Modules	2 modules
Material	ASA + PC: mechanism cover
Fixing Mode	Clip-in
Depth	28 mm
Width	45 mm
Height	45 mm
Embedding Depth	18 mm
Net Weight	0.073 kg

Environment

Ip Degree Of Protection	IP20
Ik Degree Of Protection	IK01
Ambient Air Temperature For Operation	15...35 °C
Ambient Air Temperature For Storage	0...35 °C

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Environmental Characteristic	UV resistant Bleach Window-cleaning fluid Liquid soap Acetone Oil Alcohol Petrol
Standards	EN 50083-4 EMC directive UNE 20-523-79 (2e) DIN 45325 DIN 45330 R.D. 1/1998 EN 50083-1 R.D. 279/1999 EN 50083-2

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	4.000 cm
Package 1 Width	6.500 cm
Package 1 Length	6.500 cm
Package 1 Weight	72.800 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	10
Package 2 Height	4.500 cm
Package 2 Width	13.500 cm
Package 2 Length	33.500 cm
Package 2 Weight	804.000 g
Unit Type Of Package 3	S02
Number Of Units In Package 3	40
Package 3 Height	15.000 cm
Package 3 Width	30.000 cm
Package 3 Length	40.000 cm
Package 3 Weight	3.444 kg

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency RoHS/REACH

Well-being performance

✓	Reach Free Of Svhc	
✓	Toxic Heavy Metal Free	
✓	Mercury Free	
✓	Rohs Exemption Information	Yes

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	No need of specific recycling operations