


Product data sheet

Specifications



Unica - SAT single shield socket - male individual - white

MGU3.462.18

 **Discontinued on:** Dec 31, 2023

 **Discontinued**

Main

Range	Unica
Aesthetic Name	Unica (standard aesthetic)
Product Or Component Type	SAT socket
Device Presentation	Mechanism
Tv Socket Type	Individual
Colour Tint	White

Complementary

Sat Connector	Male IEC 9.52 mm
Path Attenuation	11 dB TV signal5...2150 MHz
Dc Current Flow	No
Number Per Line	1
Number Of Modules	2 modules
Material	ASA + PC: mechanism cover
Fixing Mode	Clip-in
Depth	28 mm
Width	45 mm
Height	45 mm
Embedding Depth	18 mm
Net Weight	0.073 kg

Environment

Ip Degree Of Protection	IP20
Ik Degree Of Protection	IK01
Ambient Air Temperature For Operation	15...35 °C
Ambient Air Temperature For Storage	0...35 °C
Environmental Characteristic	Oil UV resistant Acetone Petrol Liquid soap Alcohol Bleach Window-cleaning fluid

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Standards	EN 50083-2 EN 50083-4 EN 50083-1 UNE 20-523-79 (2e) DIN 45325 R.D. 1/1998 EMC directive R.D. 279/1999 DIN 45330
-----------	---

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	4.000 cm
Package 1 Width	6.500 cm
Package 1 Length	6.500 cm
Package 1 Weight	58.000 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	10
Package 2 Height	4.500 cm
Package 2 Width	13.500 cm
Package 2 Length	33.000 cm
Package 2 Weight	645.000 g
Unit Type Of Package 3	S02
Number Of Units In Package 3	40
Package 3 Height	15.000 cm
Package 3 Width	30.000 cm
Package 3 Length	40.000 cm
Package 3 Weight	2.852 kg

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency RoHS/REACH

Well-being performance

✓ Reach Free Of Svhc

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information [Yes](#)

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations