


# Product data sheet

Specifications



## Unica - rotary dimmer - 127/230 VAC - 40...400 W/VA - ivory

MGU3.559.25

 **Discontinued on:** Dec 31, 2017

 **Discontinued**

### Main

Aesthetic Name	Unica (standard aesthetic)
Product Or Component Type	Dimmer
Device Presentation	Mechanism
Fixing Mode	Clip-in
[Ue] Rated Operational Voltage	127 V AC 50/60 Hz 230 V AC 50/60 Hz
Number Of Modules	1 module
Colour Tint	Ivory

### Complementary

Dimmer Control	Rotary push type
Total Number Of Wires	2
Load Type	127 V AC halogen lamp - 40...250 W 127 V AC incandescent lamp - 40...250 W 230 V AC halogen lamp - 60...400 W 230 V AC incandescent lamp - 60...400 W
Fuse Type	4 Ah 5 x 20 mm 127 V 50/60 Hz 4 Ah 5 x 20 mm 230 V 50/60 Hz
Marking	L+N
Connections - Terminals	Screw terminals
Clamping Connection Capacity	<= 2 x 2.5 mm² for flexible cable(s) <= 2 x 2.5 mm² for rigid cable(s)
Material	ASA + PC: mechanism cover
Standards	IEC 60669-1, 1998-Ed.3 + A1, 1999 IEC 60669-2-1, 2002-Ed.4
Product Certifications	NOM/ANCE CE
Ambient Air Temperature For Operation	5...30 °C
Ambient Air Temperature For Storage	-20...60 °C
Embedding Depth	34 mm
Depth	50 mm
Width	22.5 mm
Height	45 mm
Net Weight	0.09 kg

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

## Environment

<b>Ik Degree Of Protection</b>	IK01
<b>Ip Degree Of Protection</b>	IP20
<b>Environmental Characteristic</b>	Oil UV resistant Acetone Alcohol Petrol Liquid soap Bleach Window-cleaning fluid

## Packing Units

<b>Unit Type Of Package 1</b>	PCE
<b>Number Of Units In Package 1</b>	1
<b>Package 1 Height</b>	6.5 cm
<b>Package 1 Width</b>	8.7 cm
<b>Package 1 Length</b>	8 cm
<b>Package 1 Weight</b>	90 g

## Contractual warranty

<b>Warranty</b>	18 months
-----------------	-----------

# Sustainability

**Green Premium™ label** is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)



Transparency   RoHS/REACH

## Certifications & Standards

<b>Eu Rohs Directive</b>	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
<b>Environmental Disclosure</b>	<a href="#">Product Environmental Profile</a>
<b>Circularity Profile</b>	<a href="#">End of Life Information</a>