


Product data sheet

Specifications



Unica Quadro Pearl - cover frame - 2 gangs, H71/V71 - salmon

MGU4.704.37

⚠ Discontinued on: Sep 30, 2023

⚠ Discontinued

Main

Range	Unica
Device Application	Mounting
Product Or Component Type	Cover frame
Aesthetic Name	Unica Quadro
Number Of Gangs	2 gangs horizontal 2 gangs vertical
Fixing Mode	Clip-in
Cover Frame Colour Tint	Salmon

Complementary

Material	ABS (acrylonitrile butadiene-styrene): cover frame
Standards	EN 60669-1
Height	87 mm
Width	158 mm
Depth	14 mm
Distance Between Centers	71 mm
Net Weight	0.028 kg
Market Segment	Small commercial Residential

Environment

Ik Degree Of Protection	IK01
Ip Degree Of Protection	IP20
Environmental Characteristic	Petrol UV resistant Bleach Window-cleaning fluid Liquid soap Alcohol Oil Acetone

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 1 Height	1.500 cm
Package 1 Width	8.500 cm
Package 1 Length	16.000 cm
Package 1 Weight	26.500 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	5
Package 2 Height	6.500 cm
Package 2 Width	12.500 cm
Package 2 Length	18.500 cm
Package 2 Weight	189.000 g
Unit Type Of Package 3	S01
Number Of Units In Package 3	20
Package 3 Height	15.000 cm
Package 3 Width	15.000 cm
Package 3 Length	40.000 cm
Package 3 Weight	917.000 g

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency RoHS/REACH

Well-being performance



Mercury Free



RoHS Exemption Information

Yes

Certifications & Standards

Reach Regulation

[REACH Declaration](#)

Eu RoHS Directive

Compliant with Exemptions

China RoHS Regulation

[China RoHS declaration](#)

Product out of China RoHS scope. Substance declaration for your information

Environmental Disclosure

[Product Environmental Profile](#)

Weee

The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

Circularity Profile

No need of specific recycling operations