

# Product data sheet

Specifications



## Unica - Double USB charger - 2.1 A - white

MGU5.418.18ZD

⚠ Discontinued on: Jun 15, 2023

⚠ Discontinued

### Main

Range	Unica
Product Or Component Type	USB charger
Device Presentation	Mechanism with fixing frame

### Complementary

Device Application	Charger
Device Mounting	Flush
Number Of Modules	2 modules
Type Of Usb Power Supply	USB type A + A
Colour Tint	White (RAL 9003)
Surface Finish	Glossy
[Ue] Rated Operational Voltage	100...240 V AC 50/60 Hz +/- 10 %
Power Consumption In W	0.1 W
Nominal Output Power	10.5 W
Input Power	12 W
Service Life In Hours	30000 h 10.5 W
Socket Number	2
Integrated Connection Type	2 USB 2.0 port 5 V DC, maximum load current: 2.1 A
Material	ABS (acrylonitrile butadiene-styrene): centre plate PC (polycarbonate) GF10 FR: casing PC (polycarbonate) GF10 FR: internal cover
Protection Type	Short-circuit protection
Number Of Terminals	2 screw terminals
Shape Of Screw Head	Pozidriv No 1
Clamping Connection Capacity	2 x 0.75...2 x 2.5 mm² for rigid cable(s) 2 x 0.75...2 x 2.5 mm² for flexible cable(s) 2 x 0.75...2 x 2.5 mm² for stranded cable(s)
Wire Stripping Length	8 mm
Product Compatibility	All devices fulfilling the EN 62684 standard
Fixing Mode	Screws or claws
Type Of Packing	Flow-pack
Ambient Air Temperature For Operation	-5...40 °C

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Ambient Air Temperature For Storage	-5...50 °C
Standards	2004/108/EC EN 60950-1 EN 62684 ETSI EN 301 489-4 EU directive 2002/95/EC 2006/95/EC
Height	71 mm
Width	71 mm
Depth	42 mm
Embedding Depth	30.8 mm
Net Weight	0.088 kg

## Environment

Electrical Insulation Class	Class II
Ik Degree Of Protection	IK04
Ip Degree Of Protection	IP20

## Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	4.5 cm
Package 1 Width	7.5 cm
Package 1 Length	7.5 cm
Package 1 Weight	80 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	10
Package 2 Height	8 cm
Package 2 Width	20 cm
Package 2 Length	22.5 cm
Package 2 Weight	905 g
Unit Type Of Package 3	P06
Number Of Units In Package 3	160
Package 3 Height	75 cm
Package 3 Width	80 cm
Package 3 Length	60 cm
Package 3 Weight	26.272 kg

# Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

Eu Rohs Directive	Under investigation
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins