

Product data sheet

Specifications



Unica Top/Class - 1 RJ45 socket (S-One) - 2 m - Cat.5e, UTP - graph.

MGU5.421.12ZD

 **Discontinued on:** Jun 15, 2023

 **Discontinued**

Main

Range	Unica
Aesthetic Name	Unica Top - Unica Class
Product Or Component Type	Data socket
Device Application	Communication
Device Presentation	Mechanism with fixing frame
Colour Tint	Graphite
Data Socket Type	RJ45 4 contact(s) Cat.5e < 155 MHz
Provided Equipment	Label holder Protective flap

Complementary

Communication Network Type	1000BASE-T
Communication Port Protocol	ATM 155 Mbps
Number Of Modules	2 modules
Socket Number	1
Type Of Footprint	Infraplus
Connector Type	S-One
Cable Shielding Type	U/UTP
Organization Of Wire	Unshielded twisted pair
Connections - Terminals	Click
Marking	Colour coding
Device Mounting	Flush
Fixing Mode	Screws By screw: shield
Installation Direction	Straight
Material	ABS (acrylonitrile butadiene-styrene): mechanism cover Zamak: fixing frame
Depth	36 mm
Width	70.9 mm
Height	70.9 mm
Embedding Depth	25 mm
Net Weight	0.051 kg

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Environment

Ip Degree Of Protection	IP40
Ik Degree Of Protection	IK01
Ambient Air Temperature For Operation	15...30 °C
Ambient Air Temperature For Storage	0...35 °C
Environmental Characteristic	Oil UV resistant Alcohol Liquid soap Bleach Acetone Window-cleaning fluid Petrol
Standards	ISO 8877

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	4.0 cm
Package 1 Width	7.5 cm
Package 1 Length	7.5 cm
Package 1 Weight	52.0 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	10
Package 2 Height	8.0 cm
Package 2 Width	20.0 cm
Package 2 Length	22.5 cm
Package 2 Weight	615.0 g
Unit Type Of Package 3	S03
Number Of Units In Package 3	50
Package 3 Height	30.0 cm
Package 3 Width	30.0 cm
Package 3 Length	40.0 cm
Package 3 Weight	3.462 kg

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

Eu Rohs Directive	Under investigation
Circularity Profile	No need of specific recycling operations