

Product data sheet

Specifications



Unica Plus - cover frame - 2 gangs, H71 - light grey/ivory

MGU6.004.524

⚠ Discontinued on: Sep 30, 2023

⚠ Discontinued

Main

Range	Unica
Device Application	Mounting
Product Or Component Type	Cover frame
Aesthetic Name	Unica Plus
Number Of Gangs	2 gangs horizontal
Fixing Mode	Clip-in
Cover Frame Colour Tint	Light grey
Decoration Colour	Ivory

Complementary

Material	ABS (acrylonitrile butadiene-styrene): cover frame
Standards	EN 60669-1
Height	80 mm
Width	161 mm
Depth	14 mm
Distance Between Centers	71 mm
Net Weight	0.035 kg
Market Segment	Residential Small commercial

Environment

Ik Degree Of Protection	IK01
Ip Degree Of Protection	IP20
Environmental Characteristic	Bleach Oil Petrol UV resistant Acetone Alcohol Window-cleaning fluid Liquid soap

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 1 Height	1 cm
Package 1 Width	16 cm
Package 1 Length	8 cm
Package 1 Weight	35 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	5
Package 2 Height	6.5 cm
Package 2 Width	12.4 cm
Package 2 Length	18.5 cm
Package 2 Weight	232 g
Unit Type Of Package 3	S03
Number Of Units In Package 3	80
Package 3 Height	30 cm
Package 3 Width	30 cm
Package 3 Length	40 cm
Package 3 Weight	4.2 kg

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency RoHS/REACH

Well-being performance

✓ Mercury Free

✓ Rohs Exemption Information [Yes](#)

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations