

Product data sheet

Specifications



Front face, Resi9 MP, 1 row of 6 modules, translucent

MIP30106T

⚠ Discontinued on: Jun 30, 2023

⚠ Discontinued

Main

Range	Resi9
Product Or Component Type	Front face
Type Of Front Plate	Transparent
Accessory / Separate Part Category	Installation accessory
Range Compatibility	Resi9 Resi9 MP

Complementary

Enclosure Mounting	Flush
Type Of Front Cover	Translucid
Number Of Horizontal Rows	1
Number Of 18 Mm Modules Per Row	6
Total Number Of 18 Mm Modules	6
Enclosure Material	Door: technoplastic Front face: technoplastic
Width	186 mm outside:
Height	252 mm outside:
Depth	13 mm wall: 17 mm outside:
Colour	Front face: white (RAL 9003)

Environment

Standards	IEC 529 EN 50102 IEC 60695-2-11
Fire Resistance	Door: 650 °C Front face: 650 °C
Ik Degree Of Protection	IK07
Ambient Air Temperature For Operation	-25...60 °C

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	3.0 cm

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 1 Width	18.6 cm
Package 1 Length	25.2 cm
Package 1 Weight	190.0 g
Unit Type Of Package 2	P12
Number Of Units In Package 2	384
Package 2 Height	120.0 cm
Package 2 Width	80.0 cm
Package 2 Length	120.0 cm
Package 2 Weight	119.52 kg

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability

Green Premium™ label is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)



Transparency RoHS/REACH

Well-being performance

✓ Mercury Free

✓ Rohs Exemption Information [Yes](#)

✓ Halogen Free Product

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations