


# Product data sheet

Specifications



## Supporting plates for modular jack connector, red

MTN4566-0006

### Main

|                           |                   |
|---------------------------|-------------------|
| Range                     | Merten            |
| Product Or Component Type | Central plate     |
| Device Presentation       | With fixing frame |
| Colour Tint               | Red               |

### Complementary

|                        |                              |
|------------------------|------------------------------|
| Device Mounting        | Flush                        |
| Product Destination    | Universal keystone connector |
| Connector Type         | RJ45                         |
| Fixing Mode            | By screws                    |
| Socket Number          | 2                            |
| Installation Direction | Straight                     |
| Material               | Thermoplastic                |
| Height                 | 71 mm                        |
| Width                  | 71 mm                        |

### Packing Units

|                              |           |
|------------------------------|-----------|
| Unit Type Of Package 1       | PCE       |
| Number Of Units In Package 1 | 1         |
| Package 1 Height             | 1.100 cm  |
| Package 1 Width              | 7.000 cm  |
| Package 1 Length             | 7.100 cm  |
| Package 1 Weight             | 22.000 g  |
| Unit Type Of Package 2       | BB1       |
| Number Of Units In Package 2 | 5         |
| Package 2 Height             | 8.700 cm  |
| Package 2 Width              | 8.900 cm  |
| Package 2 Length             | 12.600 cm |
| Package 2 Weight             | 152.000 g |
| Unit Type Of Package 3       | CAR       |
| Number Of Units In Package 3 | 90        |

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

|                  |           |
|------------------|-----------|
| Package 3 Height | 19.800 cm |
| Package 3 Width  | 30.300 cm |
| Package 3 Length | 40.500 cm |
| Package 3 Weight | 3.116 kg  |

## Contractual warranty

|          |           |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|

## Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency   RoHS/REACH

## Well-being performance

✓ Reach Free Of Svhc

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information   Yes

## Certifications & Standards

|                          |   |
|--------------------------|---|
| Reach Regulation         | <a href="#">REACH Declaration</a>   |
| Eu Rohs Directive        | Pro-active compliance (Product out of EU RoHS legal scope)<br><a href="#">EU RoHS Declaration</a>           |
| China Rohs Regulation    | <a href="#">China RoHS declaration</a><br>Pro-active China RoHS declaration (out of China RoHS legal scope) |
| Environmental Disclosure | <a href="#">Product Environmental Profile</a>   |
| Circularity Profile      | No need of specific recycling operations  |