

Product data sheet

Specifications



2 Push-button, make contact, 10 A,
AC 250 V, screwless, Merten

MTN3155-0000

Main

Range	Merten
Product Or Component Type	Push-button
Device Application	Lighting
Device Presentation	Mechanism with fixing frame
Technology Type	Electromechanical
Device Mounting	Flush
Number Of Rocker	2
Actuator	Rocker

Complementary

Contacts Type And Composition	1 NO
[Ue] Rated Operational Voltage	250 V
Network Type	AC
Rated Current	10 A
Connections - Terminals	Screwless terminals
Fixing Mode	By screws and claws

Environment

Ip Degree Of Protection	IP20
-------------------------	------

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	4.100 cm
Package 1 Width	7.300 cm
Package 1 Length	10.700 cm
Package 1 Weight	64.000 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	10
Package 2 Height	9.600 cm
Package 2 Width	18.600 cm
Package 2 Length	27.500 cm

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 2 Weight	746.000 g
Unit Type Of Package 3	CAR
Number Of Units In Package 3	60
Package 3 Height	30.300 cm
Package 3 Width	33.900 cm
Package 3 Length	40.200 cm
Package 3 Weight	4.944 kg

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency RoHS/REACH

Well-being performance

✓ Reach Free Of Svhc

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information [Yes](#)

Environmental Certifications

✓ Cradle To Cradle Silver

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations