


# Product data sheet

Specifications



Lower sup. Ver. Busbars In 3200A  
10mm bars. Bar distance 115mm.  
For 800mm widths

NSYAS800L

## Main

Range	Spacial
Accessory / Separate Part Category	Support accessory
Product Or Component Type	Bar support
Anwendung	Multi-purpose Prisma application
Enclosure Nominal Dimensions	-
Mounting Location	Bottom
Busbar Position	Vertical
Range Compatibility	Lineryg Linergy LGYE Lineryg Linergy BS Spacial Spacial SFP

## Complementary

Cubicle-Device Connection	Lineryg LGYE lateral busbar Lineryg BS lateral busbar
Device Composition	fixing elements 1 insulating bar support 1 metal support
Quantity Per Set	Set of 1
Material	Bar support: plastic Metal support: steel
Fixing Mode	By fixing element - bottom frame of enclosure location
Height	66 mm
Width	750 mm fixing centers: 800 mm nominal:
Depth	39 mm

## Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	4.0 cm
Package 1 Width	10.0 cm
Package 1 Length	78.5 cm
Package 1 Weight	2.188 kg
Unit Type Of Package 2	P12

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Number Of Units In Package 2	50
Package 2 Height	45.0 cm
Package 2 Width	80.0 cm
Package 2 Length	120.0 cm
Package 2 Weight	125.0 kg

## Contractual warranty

Warranty	18 months
----------	-----------

# Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency   RoHS/REACH

## Well-being performance

✓ Mercury Free

✓ Rohs Exemption Information   [Yes](#)

## Certifications & Standards

Reach Regulation	<a href="#">REACH Declaration</a>
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	<a href="#">China RoHS declaration</a> Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations