


Product data sheet

Specifications



ClimaSys CA - CSVS External SmartGrid for cut-out 291x291mm

NSYCAG291DGC

 **Discontinued on:** Jul 3, 2023

 **Discontinued**

Main

Range	ClimaSys
Product Name	ClimaSys CA
Product Or Component Type	Outlet grille cover
Device Application	To digitize a standard ClimaSys CV fan To replace an existing ClimaSys DG grille To make visible the LEDs status To inform about ventilation reliability from the dust sensor
Range Compatibility	ClimaSys CV ClimaSys DG
Accessory / Separate Part Category	Thermal management accessory Spare part
Accessory / Separate Part Destination	ClimaSys ventilation system
Fixing Mode	Clipped
Quantity Per Set	Set of 1

Complementary

Material	Injected thermoplastic (PC)
Colour	Smoked black (RAL 9005)
Cut-Out Dimensions	291 x 291 mm
Width	316 mm external:
Height	336 mm external:
Ip Degree Of Protection	IP54 fan IP54 grille
Depth	13 mm external:
Device Composition	1 x smart filter with dust sensor 1 x outlet grille cover

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	5.0 cm
Package 1 Width	32.5 cm
Package 1 Length	34.5 cm
Package 1 Weight	538.0 g

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Unit Type Of Package 2	CAR
Number Of Units In Package 2	6
Package 2 Height	30.0 cm
Package 2 Width	39.5 cm
Package 2 Length	40.0 cm
Package 2 Weight	3.704 kg

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency RoHS/REACH

Well-being performance



Mercury Free



RoHS Exemption Information

Yes

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile