

Product data sheet

Specifications



Mureva Styl - fixing frame - 1 gang - white

MUR39107

Main

Range Of Product	Mureva Styl
Product Or Component Type	Fixing frame
Range Compatibility	Mureva Styl
Colour Tint	White (RAL 9003)

Complementary

Device Mounting	Flush
Number Of Gangs	1 gang
Condition Of Use	Indoor/outdoor
Material	PC
Length	84 mm
Height	28 mm
Width	84 mm
Projecting Depth	19 mm

Chemical And Detergent Products Resistance	Resistant to alcohol (70 %) Resistant to alcohol (96 %) Resistant to A-Lactic Acid Resistant to diluted quaternary ammonium Resistant to diluted bleach Resistant to diluted ammonia Resistant to soapy water Resistant to crystal cleaner Resistant to hydrogen peroxide 10 volumes Resistant to hexane
--	---

Environment

Quality Labels	AENOR NF
Ip Degree Of Protection	IP55
Ik Degree Of Protection	IK08
Flame Retardance	Self-extinguishing 650 °C conforming to IEC 60695-2-1
Ambient Air Temperature For Operation	-5...40 °C
Ambient Air Temperature For Storage	-25...55 °C

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 1 Height	2.600 cm
Package 1 Width	8.400 cm
Package 1 Length	8.400 cm
Package 1 Weight	40.000 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	10
Package 2 Height	9.000 cm
Package 2 Width	17.000 cm
Package 2 Length	40.000 cm
Package 2 Weight	490.000 g
Unit Type Of Package 3	S04
Number Of Units In Package 3	60
Package 3 Height	30.000 cm
Package 3 Width	40.000 cm
Package 3 Length	60.000 cm
Package 3 Weight	3.738 kg

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Sustainable Packaging

Resource performance

✔ Sustainable Packaging

Well-being performance

✔ Mercury Free

✔ Rohs Exemption Information Yes

Reach Regulation REACH Declaration

Eu Rohs Directive Pro-active compliance (Product out of EU RoHS legal scope)

China Rohs Regulation China RoHS declaration
Product out of China RoHS scope. Substance declaration for your information