

Product data sheet

Specifications



Hexagonal spacers M6 height 100
for raising mounting plates, etc.
Supply: 100

NSYEX1006

Main

Category	Mounting accessory
Product Or Component Type	Spacer
Range Compatibility	Spacial Spacial CRN Spacial Spacial S3D Spacial Spacial S3CM
Application	Multi-purpose
Nominal Dimensions Of The Housing	-
Mounting Location	Other hexagonal spacer Switchgear On mounting plate
Device Composition	1 spacer
Quantity Per Set	Set of 100
Material	Galvanised steel

Complementary

Fixing Mode	Screw-on
Height	100 mm
Iso Thread	M6

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	1.000 cm
Package 1 Width	1.000 cm
Package 1 Length	11.000 cm
Package 1 Weight	53.000 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	100
Package 2 Height	9.500 cm
Package 2 Width	13.500 cm
Package 2 Length	21.500 cm
Package 2 Weight	5.366 kg
Unit Type Of Package 3	S03

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Number Of Units In Package 3	400
Package 3 Height	30 cm
Package 3 Width	30 cm
Package 3 Length	40 cm
Package 3 Weight	21.884 kg

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency RoHS/REACH

Well-being performance

✓ Reach Free Of Svhc

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information Yes

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations