


Product data sheet

Specifications



Microperforated mounting plate H800xW600 w/holes diam 3,6mm on 12,5mm pitch

NSYMF86

Main

Range	Spacial
Accessory / Separate Part Category	Mounting accessory
Product Or Component Type	Mounting plate
Device Application	Multi-purpose
Enclosure Nominal Dimensions	- H: 800 mm W: 600 mm
Mounting Location	Step slide Direct fixing on backstuds
Mounting Plate Description	Microperforated
Range Compatibility	Spacial Spacial S3D Spacial Spacial CRN Spacial Spacial S3X
Quantity Per Set	Set of 1
Material	Galvanised steel

Complementary

Fixing Mode	Screwed on backstuds - screw type M8 By fixing element
Permanent Permissible Load	135 kg
Height	765 mm
Width	550 mm
Depth	125 mm
Thickness	2.5 mm
Net Weight	7.8 kg
Variant Particularity	With enclosures H800 x W1200 Installation in enclosures with inverted dimensions

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	0.3 cm
Package 1 Width	55.5 cm
Package 1 Length	76.5 cm
Package 1 Weight	7.67 kg
Unit Type Of Package 2	PAM

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Number Of Units In Package 2	80
Package 2 Height	31.0 cm
Package 2 Width	100.0 cm
Package 2 Length	120.0 cm
Package 2 Weight	667.0 kg

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency RoHS/REACH

Well-being performance

✓	Reach Free Of Svhc	
✓	Toxic Heavy Metal Free	
✓	Mercury Free	
✓	Rohs Exemption Information	Yes

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations