

Product data sheet

Specifications



Plain mounting plate H200xW800mm made of galvanised sheet steel

NSYMM28SB

Main

Range	Spacial
Accessory / Separate Part Category	Mounting accessory
Product Or Component Type	Mounting plate
Device Application	Multi-purpose
Enclosure Nominal Dimensions	-
Mounting Location	Bottom of enclosure
Mounting Plate Description	Plain
Range Compatibility	Spacial Spacial SBM
Device Composition	1 mounting plate
Material	Galvanised steel
Surface Finish	Metallic

Complementary

Fixing Mode	By 2 screws - screw type Ø5 mm self-tapping screws - bottom of enclosure location
Permanent Permissible Load	8 kg back of the enclosure
Height	175 mm nominal:
Width	785 mm nominal: 764 mm fixing centers:
Surface And Useful Surface	Nominal: 160000 mm²
Thickness	2 mm
Net Weight	2.106 kg

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	0.3 cm
Package 1 Width	18.0 cm
Package 1 Length	79.0 cm
Package 1 Weight	2.106 kg
Unit Type Of Package 2	PAM
Number Of Units In Package 2	200
Package 2 Height	45.0 cm

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 2 Width	100.0 cm
Package 2 Length	120.0 cm
Package 2 Weight	439.206 kg

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency RoHS/REACH

Well-being performance

✓ Reach Free Of Svhc

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information Yes

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations