


# Product data sheet

Specifications

## 19" fixed shelf 1U on 2 uprights D250 with permissive load 15Kg



NSYBF1U25P

### Overview

Presentation	Power Management
Lead Time	Usually Ships within 4 Weeks

### Main

Range Of Product	Actassi
Product Or Component Type	Fixed shelf
Accessory / Separate Part Type	Fixed perforated shelf
Device Application	Multi-purpose Electronic application
Colour	Grey (RAL 7035)

### Complementary

Range Compatibility	Actassi VDA Actassi VDS
Material	Sheet steel
Surface Finish	Epoxy-polyester powder
Mounting Support	19" rack, front or rear
Product Compatibility	Spacial SF-S, SF-E, VDM, PLA enclosures
Fixing Mode	By 19" fixing element: 19" uprights of rack
Number Of Rack Unit	1U
Permanent Permissible Load	15 kg
Thickness	5 mm
Number Of Units 19"	1
Height	44.45 mm
Width	465 mm
Depth	250 mm

### Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	9.65 cm
Package 1 Width	23.11 cm
Package 1 Length	50.04 cm

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 1 Weight	1.73 kg
Unit Type Of Package 2	PAM
Number Of Units In Package 2	42
Package 2 Height	73 cm
Package 2 Width	100 cm
Package 2 Length	120 cm
Package 2 Weight	85 kg

## Contractual warranty

Warranty	18 months
----------	-----------

# Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency   RoHS/REACH

## Well-being performance

✓ Mercury Free

✓ Rohs Exemption Information   [Yes](#)

## Certifications & Standards

Reach Regulation	<a href="#">REACH Declaration</a>
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	<a href="#">China RoHS declaration</a> Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations