

Product data sheet

Specifications



Hinged plain cover plate, PanelSeT SFN, Spacial SF, Spacial SM, for electrical enclosure W600mm steel, H600mm

NSYMPCH606

Main

Range	Spacial
Accessory / Separate Part Category	Enclosure accessory
Product Or Component Type	Cover plate
Anwendung	Multi-purpose
Range Compatibility	Spacial Spacial SF Spacial Spacial SM
Nominal Dimensions Of The Housing	- H: 600 mm W: 600 mm
Mounting Location	On chassis coupling set
Device Composition	fixing elements 1 cover plate hinges
Quantity Per Set	Set of 1

Complementary

Material	Steel
Colour	Grey (RAL 7035)
Surface Finish	Epoxy-polyester powder
Fixing Mode	By screws
Type Of Front Plate	Hinged plain
Height	600 mm nominal: 599.5 mm real:
Width	600 mm nominal: 478 mm fixing centers: 502 mm real:
Depth	12 mm real:

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	2.0 cm
Package 1 Width	50.5 cm
Package 1 Length	60.5 cm
Package 1 Weight	5.008 kg
Unit Type Of Package 2	PAM

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Number Of Units In Package 2	50
Package 2 Height	63.0 cm
Package 2 Width	100.0 cm
Package 2 Length	120.0 cm
Package 2 Weight	263.0 kg

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency RoHS/REACH

Well-being performance

✓ Mercury Free

✓ Rohs Exemption Information [Yes](#)

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations