

Product data sheet

Specifications



reversible internal door polyester 2 locks grid pattern forPLM54

NSYPAP54G

Main

Range	Thalassa
Accessory / Separate Part Category	Enclosure accessory
Product Or Component Type	Door
Application	Multi-purpose
For Enclosure Nominal Dimensions	-
Mounting Location	Front side
Range Compatibility	Thalassa Thalassa PLM
Device Composition	1 door 1 handle 4 fixing brackets

Complementary

Material	Polyester charged with fibreglass
Colour	Grey (RAL 7035)
Lock Type	Lock 5 mm double bar
Number Of Locks	2
Door Type	Internal plain
Door Opening Side	Reversible (110 °)
Height	Grid pattern: 415 mm
Width	Grid pattern: 305 mm
Depth	26 mm available depth between enclosure door: 152 mm available depth between rear:

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	5.4 cm
Package 1 Width	36.9 cm
Package 1 Length	50.1 cm
Package 1 Weight	1.669 kg
Unit Type Of Package 2	CAR
Number Of Units In Package 2	5
Package 2 Height	38.9 cm

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 2 Width	29.3 cm
Package 2 Length	51.1 cm
Package 2 Weight	8.345 kg
Unit Type Of Package 3	PAM
Number Of Units In Package 3	80
Package 3 Height	120 cm
Package 3 Width	100 cm
Package 3 Length	90 cm
Package 3 Weight	153 kg

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency RoHS/REACH

Well-being performance

✓ Mercury Free

✓ Rohs Exemption Information [Yes](#)

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations