

# Product data sheet

Specifications



PLS box, polyester rear, transparent  
PC cover IP66 54x54x18cm

NSYPLS5454G

## Main

|                     |  |
|---------------------|--|
| Range               | Thalassa   |
| Product Name        | Thalassa PLS   |
| Device Short Name   | PLS  |
| Enclosure Type      | Multi-purpose  |
| Category            | Insulating modular box   |
| Nominal Height      | 540 mm   |
| Nominal Width       | 540 mm   |
| Nominal Depth       | 180 mm   |
| Enclosure Mounting  | Wall mounted   |
| Device Composition  | 1 cover: on enclosure<br>1 rear part: on enclosure<br>locking screws |
| Body Type           | One piece moulded  |
| Type Of Front Cover | Low transparent cover  |
| Lock Type           | Slot screw   |

## Complementary

|                        |  |
|------------------------|--|
| Removable Parts        | Cover locking screw  |
| Material               | Cover: polycarbonate<br>Rear: polyester reinforced with fibreglass |
| Colour                 | Body: grey (RAL 7035)  |
| Standards              | NEMA classification 13<br>IEC 62208<br>NEMA 4X                     |
| Product Certifications | UL   |

## Environment

|                                     |                                |
|-------------------------------------|--------------------------------|
| Electrical Insulation Class         | Class II                       |
| Ip Degree Of Protection             | IP66 conforming to IEC 60529   |
| Ik Degree Of Protection             | IK09 conforming to IEC 62262   |
| Fire Resistance                     | 960 °C conforming to IEC 62208 |
| Ambient Air Temperature For Storage | -30...70 °C                    |

## Packing Units

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

|                              |         |
|------------------------------|---------|
| Unit Type Of Package 1       | PCE     |
| Number Of Units In Package 1 | 1       |
| Package 1 Height             | 20.0 cm |
| Package 1 Width              | 56.0 cm |
| Package 1 Length             | 56.0 cm |
| Package 1 Weight             | 5.85 kg |
| Unit Type Of Package 2       | PAM     |
| Number Of Units In Package 2 | 30      |
| Package 2 Height             | 120 cm  |
| Package 2 Width              | 100 cm  |
| Package 2 Length             | 185 cm  |
| Package 2 Weight             | 200 kg  |

## Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency   RoHS/REACH

## Well-being performance

✓ Mercury Free

✓ Rohs Exemption Information   [Yes](#)

## Certifications & Standards

|                          |   |
|--------------------------|---|
| Reach Regulation         | <a href="#">REACH Declaration</a>   |
| Eu Rohs Directive        | Pro-active compliance (Product out of EU RoHS legal scope)  |
| China Rohs Regulation    | <a href="#">China RoHS declaration</a><br>Product out of China RoHS scope. Substance declaration for your information |
| Environmental Disclosure | <a href="#">Product Environmental Profile</a>   |
| Circularity Profile      | No need of specific recycling operations  |