

# Product data sheet

Specifications



## Modular chassis DLM type for SPACIAL WM enclosure, 24 modules, H400xW300mm.

NSYDLM24

### Main

Range	Spacial
Accessory / Separate Part Category	Mounting accessory
Application	Modular distribution application Multi-purpose
Product Or Component Type	Chassis
Device Short Name	DLM
For Enclosure Nominal Dimensions	-
Mounting Location	Front of enclosure Step slide
Range Compatibility	Spacial Spacial S3D Spacial Spacial S3X Spacial Spacial CRN
Device Composition	1 chassis structure 2 finish cover 1 neutral/earth strip 2 x 16 mm <sup>2</sup> 5 x 6 mm <sup>2</sup> 2 front panels with 35 mm DIN rail
Quantity Per Set	Set of 1

### Complementary

Material	Steel
Colour	Front panel: grey (RAL 7035)
Surface Finish	Polyester powder
Fixing Mode	By fixing element - on front and back with supports location
Adjustment	In height from 40 to 85 mm for DIN rail
Number Of Horizontal Rows	2
Total Number Of 18 Mm Modules	24
Type Of Front Plate	Plain and cut-out plates
Number Of Cut-Out	2 cut-outs
Height	353 mm
Width	255 mm
Depth	101.5 mm

### Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 1 Height	11.500 cm
Package 1 Width	27.000 cm
Package 1 Length	36.500 cm
Package 1 Weight	2.548 kg
Unit Type Of Package 2	S04
Number Of Units In Package 2	4
Package 2 Height	30 cm
Package 2 Width	40 cm
Package 2 Length	60 cm
Package 2 Weight	10.842 kg

## Contractual warranty

Warranty	18 months
----------	-----------

## Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency   RoHS/REACH

## Well-being performance



Mercury Free



RoHS Exemption Information

Yes

## Certifications & Standards

Reach Regulation

[REACH Declaration](#)

Eu RoHS Directive

Pro-active compliance (Product out of EU RoHS legal scope)

China RoHS Regulation

[China RoHS declaration](#)

Product out of China RoHS scope. Substance declaration for your information

Environmental Disclosure

[Product Environmental Profile](#)

Circularity Profile

No need of specific recycling operations