

Product data sheet

Specifications



S3DCD Disc. pl d w/o pl. c, w/o CGP.
H1000xW1000xD300mm.H39,37xW 31,50xD15,75Inch

NSYS3DCD101030

❗ Discontinued

❗ Discontinued on: Jun 17, 2020

❗ End-of-service on: Sep 30, 2020

Main

Range	Spacial
Product Name	Spacial S3DCD
Application	Multi-purpose
Category	Compact enclosure
Enclosure Nominal Height	1000 mm
Enclosure Nominal Width	1000 mm
Enclosure Nominal Depth	300 mm
Door Type	Plain
Mounting Plate Description	Without mounting plate
Type Of Gland Plate	Without gland plate
Installation Accessory Type	Wall-mounting
Product Destination	To house safety disconnect equipment
Device Composition	1 body 1 door 1 lock

Complementary

Body Type	Gutter-shaped front profile double sheet thickness Single piece body
Number Of Doors	Front face: 1 door(s)
Door Opening Side	Left (120 °)
Lock Type	3 points lock, screw driver insert
Accessibility For Operation	Front
Removable Parts	Door by hinges
Material	Steel
Surface Finish	Epoxy-polyester powder
Colour	Grey (RAL 7035)
Standards	IEC 62208
Product Certifications	UL
Net Weight	54 kg

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Environment

Ik Degree Of Protection	IK10 conforming to IEC 62262
Ip Degree Of Protection	IP66 conforming to IEC 60529

Contractual warranty

Warranty	18 months
-----------------	-----------

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency RoHS/REACH

Well-being performance

✓ Reach Free Of Svhc

✓ Mercury Free

✓ Rohs Exemption Information [Yes](#)

Certifications & Standards

Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile