

# Product data sheet

Specifications



## Door for wall mounting enclosure Spacial S3HD - 700x500 mm

NSYDS3HD75

### Main

|                                    |  |
|------------------------------------|--|
| Range                              | Spacial  |
| Accessory / Separate Part Category | Enclosure accessory                                      |
| Product Or Component Type          | Door   |
| Application                        | Heavy duty   |
| For Enclosure Nominal Dimensions   | - H: 700 mm W: 500 mm                                    |
| Mounting Location                  | Front  |
| Range Compatibility                | Spacial Spacial S3HD compact enclosure                   |
| Device Composition                 | 1 door<br>2 hinges<br>1 lock with 3 mm double bar insert |
| Quantity Per Set                   | Set of 1   |

### Complementary

|                   |   |
|-------------------|---|
| Material          | Door: steel with anti-corrosive coating |
| Colour            | Grey (RAL 7035)                         |
| Surface Finish    | Polyester powder                        |
| Lock Type         | Lock 3 mm double bar                    |
| Number Of Locks   | 1                                       |
| Door Type         | Plain                                   |
| Door Opening Side | Reversible (120 °)                      |
| Maximum Load      | 200 kg                                  |
| Height            | 700 mm nominal:                         |
| Width             | 500 mm nominal:                         |
| Thickness         | 1.5 mm                                  |
| Net Weight        | 4.331 kg                                |

### Environment

|                              |  |
|------------------------------|--|
| Ik Degree Of Protection      | IK10 conforming to IEC 62262   |
| Environmental Characteristic | Corrosion resistance C4H conforming to ISO 12944: 1999<br>UV resistant conforming to IEC 62208 |

### Packing Units

|                        |     |
|------------------------|-----|
| Unit Type Of Package 1 | PCE |
|------------------------|-----|

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

|                              |          |
|------------------------------|----------|
| Number Of Units In Package 1 | 1        |
| Package 1 Height             | 5.0 cm   |
| Package 1 Width              | 51.0 cm  |
| Package 1 Length             | 71.0 cm  |
| Package 1 Weight             | 4.331 kg |

# Sustainability

**Green Premium™ label** is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)

## Well-being performance

|  |   |
|--|---|
|  Mercury Free               |   |
|  Rohs Exemption Information | <a href="#">Yes</a>   |
| Reach Regulation   | <a href="#">REACH Declaration</a>   |
| Eu Rohs Directive  | Pro-active compliance (Product out of EU RoHS legal scope)  |
| China Rohs Regulation  | <a href="#">China RoHS declaration</a><br>Product out of China RoHS scope. Substance declaration for your information |