

# Product data sheet

Specifications



## Spacial SD Compact control desk w/ o mounting plate - H1000xW800xD466 - IP55

NSYSD8

### Main

Range	Spacial
Product Name	Spacial SD
Enclosure Type	Multi-purpose
Category	Monobloc control desk
Nominal Height	1000 mm
Nominal Width	800 mm
Nominal Depth	466 mm
Product Installation	Floor-standing
Device Composition	1 structure 1 door 2 lock: door 4 adjustment rail 1 cable gland plate 2 pneumatic stay: desk lid

### Complementary

Body Type	Single piece structure folded and welded
Door Type	Plain
Number Of Doors	Front: 1 door(s)
Door Opening Side	Reversible 120 ° door
Lock Type	2 points lock, 3 mm double-bar
Mounting Plate Description	Without mounting plate
Type Of Gland Plate	1 entry plate
Accessibility For Operation	Front
Removable Parts	Door by hinges Desk lid by hinges Cable gland plate by clipping screws
Material	Body: steel
Surface Finish	Epoxy-polyester powder
Thickness	1.5 mm
Colour	Grey (RAL 7035)

### Environment

Standards	IEC 62208
Ip Degree Of Protection	IP55 conforming to IEC 60529

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

<b>Ik Degree Of Protection</b>	IK10 conforming to IEC 62262
--------------------------------	------------------------------

## Packing Units

<b>Unit Type Of Package 1</b>	PCE
<b>Number Of Units In Package 1</b>	1
<b>Package 1 Height</b>	50.0 cm
<b>Package 1 Width</b>	81.0 cm
<b>Package 1 Length</b>	116.0 cm
<b>Package 1 Weight</b>	61.0 kg
<b>Unit Type Of Package 2</b>	PAM
<b>Number Of Units In Package 2</b>	2
<b>Package 2 Height</b>	131.0 cm
<b>Package 2 Width</b>	100.0 cm
<b>Package 2 Length</b>	120.0 cm
<b>Package 2 Weight</b>	137.5 kg

## Contractual warranty

<b>Warranty</b>	18 months
-----------------	-----------

# Sustainability

**Green Premium™ label** is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)



Transparency   RoHS/REACH

## Well-being performance

✓ Mercury Free

✓ Rohs Exemption Information   [Yes](#)

## Certifications & Standards

Reach Regulation	<a href="#">REACH Declaration</a>
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	<a href="#">China RoHS declaration</a> Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations