


# Product data sheet

Specifications



One symmetric mounting rail 35x7.5  
L300mm type B - Wall mounting -  
Supply: 20

NSYSDR30B

## Main

Anwendung	Multi-purpose
Range	Spacial
Product Or Component Type	Rail
Accessory / Separate Part Category	Mounting accessory
Type Of Rail	Symmetrical DIN
Enclosure Nominal Dimensions	-
Range Compatibility	Spacial Spacial CRN Spacial Spacial S3D Spacial Spacial S3X
Device Composition	fixing elements 1 rail
Quantity Per Set	Set of 20

## Complementary

Material	Zinc coated steel
Surface Finish	Zinc coated
Fixing Mode	By fixing element - structure of enclosure location
Adjustment	Pitch 25 mm Continuous adjustment
Length	Real: 250 mm Nominal: 300 mm
Height	Nominal: 7.5 mm
Width	Nominal: 35 mm
Thickness	1 mm

## Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	0.75 cm
Package 1 Width	3.5 cm
Package 1 Length	24.5 cm
Package 1 Weight	106.0 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	10

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 2 Height	4.0 cm
Package 2 Width	26.5 cm
Package 2 Length	6.0 cm
Package 2 Weight	1.064 kg
Unit Type Of Package 3	PAL
Number Of Units In Package 3	100
Package 3 Height	20.0 cm
Package 3 Width	30.0 cm
Package 3 Length	40.0 cm
Package 3 Weight	10.64 kg

## Contractual warranty

Warranty	18 months
----------	-----------

## Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency   RoHS/REACH

## Well-being performance

✓ Reach Free Of Svhc

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information   Yes

## Certifications & Standards

Reach Regulation	<a href="#">REACH Declaration</a>
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
China Rohs Regulation	<a href="#">China RoHS declaration</a> Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations