

Product data sheet

Specifications

Spacial SF ventilated roof - 800x800 mm



NSYSVR808

Main

| | |
|------------------------------------|---|
| Range | Spacial |
| Accessory / Separate Part Category | Enclosure accessory |
| Product Or Component Type | Ventilated roof |
| Device Application | Electronic application Multi-purpose |
| Mounting Location | On top of enclosure |
| Range Compatibility | Spacial Spacial SF suitable enclosure |
| Device Composition | 4 elevator 1 roof |
| Quantity Per Set | Set of 1 |

Complementary

| | |
|-------------------------|--|
| Material | Steel Plastic |
| Colour | Grey (RAL 7035) Grey |
| Surface Finish | Epoxy-polyester powder |
| Fixing Mode | By elevators - screw type M12 - roof fixing point location |
| Height | 72 mm |
| Width | 770 mm real: 800 mm nominal: |
| Depth | 770 mm real: 800 mm nominal: |
| Ip Degree Of Protection | IP30 conforming to IEC 60529 |

Packing Units

| | |
|------------------------------|---------|
| Unit Type Of Package 1 | PCE |
| Number Of Units In Package 1 | 1 |
| Package 1 Height | 8.0 cm |
| Package 1 Width | 77.5 cm |
| Package 1 Length | 78.5 cm |
| Package 1 Weight | 13.0 kg |
| Unit Type Of Package 2 | P12 |
| Number Of Units In Package 2 | 8 |

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

| | |
|------------------|----------|
| Package 2 Height | 78.0 cm |
| Package 2 Width | 80.0 cm |
| Package 2 Length | 120.0 cm |
| Package 2 Weight | 117.0 kg |

Contractual warranty

| | |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency RoHS/REACH

Well-being performance



Mercury Free



RoHS Exemption Information

Yes

Certifications & Standards

Reach Regulation

[REACH Declaration](#)

Eu RoHS Directive

Pro-active compliance (Product out of EU RoHS legal scope)

China RoHS Regulation

[China RoHS declaration](#)

Product out of China RoHS scope. Substance declaration for your information

Environmental Disclosure

[Product Environmental Profile](#)

Circularity Profile

No need of specific recycling operations