


# Product data sheet

Specifications



## Plain partial mounting plate for control desk W800mm - H447xW705 m

NSYPMP4580

 **Discontinued on:** Dec 15, 2023

 **Discontinued**

### Main

Range	Spacial
Accessory / Separate Part Category	Mounting accessory
Product Or Component Type	Mounting plate
Device Application	Multi-purpose
Enclosure Nominal Dimensions	-
Mounting Location	On adjustment rails Console upper part
Mounting Plate Description	Plain
Range Compatibility	Spacial Spacial SD
Quantity Per Set	Set of 1
Material	Galvanised steel

### Complementary

Fixing Mode	By screws - screw type M3 - slot location By screws - screw type M6 - slot location By fixing element - fixing bracket location
Height	400 mm
Width	Nominal: 800 mm Real: 650 mm
Thickness	25 mm
Variant Particularity	Order a set of 4 adjustment rails and 4 fixing brackets

### Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	1.500 cm
Package 1 Width	47.000 cm
Package 1 Length	71.000 cm
Package 1 Weight	6.500 kg
Unit Type Of Package 2	P12
Number Of Units In Package 2	14
Package 2 Height	90.000 cm

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 2 Width	80.000 cm
Package 2 Length	120.000 cm
Package 2 Weight	103.000 kg

## Contractual warranty

Warranty	18 months
----------	-----------

## Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency   RoHS/REACH

## Well-being performance

✓	Reach Free Of Svhc	
✓	Toxic Heavy Metal Free	
✓	Mercury Free	
✓	Rohs Exemption Information	Yes

## Certifications & Standards

Reach Regulation	<a href="#">REACH Declaration</a>
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
China Rohs Regulation	<a href="#">China RoHS declaration</a> Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations