

# Product data sheet

Specifications



## Cable passage IP65 w/o connectors, 14 entries.

NSYTSA2414SE

### Main

Range	Spacial
Product Or Component Type	Quick entrance plate
Accessory / Separate Part Category	Cable management accessory
Device Application	Multi-purpose
Range Compatibility	Spacial Spacial S3D compact enclosure Spacial Spacial CRN compact enclosure Spacial Spacial S3CM control enclosure Spacial Spacial SBM industrial box Thalassa Thalassa PLA suitable enclosure Thalassa Thalassa PHD suitable enclosure Thalassa Thalassa PLM compact enclosure Thalassa Thalassa PLS insulating modular box Spacial Spacial S3HD compact enclosure
Device Composition	1 fixing elements 1 plate
Quantity Per Set	Set of 1

### Complementary

Mounting Support	Body of enclosure Cable gland plate
Material	Polyamide
Fixing Mode	By fixing element
Total Cable Entry Number	14
Cable Entry Number	6 x 3...6.5 mm 4 x 5...9.2 mm 4 x 9.6...15.9 mm
Height	14 mm real:
Width	146 mm real: 112 mm cut-out: 130 mm fixing center:
Depth	58 mm real: 36 mm cut-out: 32 mm fixing centre:
Net Weight	0.16 kg

### Environment

Ip Degree Of Protection	IP65
-------------------------	------

### Packing Units

Unit Type Of Package 1	PCE
------------------------	-----

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Number Of Units In Package 1	1
Package 1 Height	3.5 cm
Package 1 Width	8 cm
Package 1 Length	17 cm
Package 1 Weight	154 g
Unit Type Of Package 2	PAL
Number Of Units In Package 2	40
Package 2 Height	20 cm
Package 2 Width	30 cm
Package 2 Length	40 cm
Package 2 Weight	6.16 kg

## Contractual warranty

Warranty	18 months
----------	-----------

# Sustainability

**Green Premium™ label** is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)



Transparency   RoHS/REACH

## Well-being performance

✓ Mercury Free

✓ Rohs Exemption Information   [Yes](#)

## Certifications & Standards

Reach Regulation	<a href="#">REACH Declaration</a>
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	<a href="#">China RoHS declaration</a> Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations