

# Product data sheet

Specifications



## Wall mounted enclosure, Spacial S3X, stainless steel 304L, plain door, 600x400x200mm, IP66

NSYS3X6420

### Main

Range	Spacial
Product name	Spacial S3X
Enclosure type	Multi-purpose
Category	Compact enclosure
Nominal height	600 mm
Nominal width	400 mm
Nominal depth	200 mm
Product installation	Wall-mounting
Device composition	1 body 1 door 2 lock: door 2 perforated vertical profile drilled: door

### Complementary

Body type	Single piece body, cross-shaped structure Gutter shaped front rail
Door type	Plain
Number of doors	Front face: 1 door(s)
Door opening side	Reversible (120 °)
Lock type	2 points lock, 3 mm double-bar
Mounting plate description	Without mounting plate
Type of gland plate	Without gland plate
Accessibility for operation	Front
Removable parts	Door by hinges
Material	Body and door: stainless steel 304L Lock: zamak Hinge: stainless steel
Surface finish	Body and door: Scotch-Brite® brushed Lock: chromium plated
Net weight	9.446 kg

### Environment

Standards	IEC 62208
-----------	-----------

<b>Product certifications</b>	UL 508 type A CAN/CSA 22
<b>IP degree of protection</b>	IP66 conforming to IEC 60529
<b>IK degree of protection</b>	IK10 conforming to IEC 62262
<b>Environmental characteristic</b>	Specific hygiene Corrosive

## Packing Units

<b>Unit Type of Package 1</b>	PCE
<b>Number of Units in Package 1</b>	1
<b>Package 1 Height</b>	21.5 cm
<b>Package 1 Width</b>	41.0 cm
<b>Package 1 Length</b>	61.0 cm
<b>Package 1 Weight</b>	9.446 kg
<b>Unit Type of Package 2</b>	PAM
<b>Number of Units in Package 2</b>	30
<b>Package 2 Height</b>	198.0 cm
<b>Package 2 Width</b>	100.0 cm
<b>Package 2 Length</b>	120.0 cm
<b>Package 2 Weight</b>	307.0 kg

## Offer Sustainability

<b>Sustainable offer status</b>	Green Premium product
<b>REACH Regulation</b>	<a href="#">REACH Declaration</a>
<b>REACH free of SVHC</b>	Yes
<b>EU RoHS Directive</b>	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
<b>Mercury free</b>	Yes
<b>China RoHS Regulation</b>	<a href="#">China RoHS declaration</a> Product out of China RoHS scope. Substance declaration for your information
<b>RoHS exemption information</b>	Yes
<b>Environmental Disclosure</b>	<a href="#">Product Environmental Profile</a>

## Contractual warranty

<b>Warranty</b>	18 months
-----------------	-----------

## Recommended replacement(s)