

Product data sheet

Specifications



Cover frame, Unica Pure, 2 gangs, white

NU6004V85

Main

Range	New Unica
Device Application	Mounting
Product Or Component Type	Cover frame
Aesthetic Name	Unica Pure
Number Of Gangs	2 gangs
Installation Direction	Vertical
Type Of Frame	Double
Number Of Modules	2 x 2 modules
Fixing Mode	Clip-in
Colour Tint	White glass
Side Color	White (RAL 9003)

Complementary

Material	Polycarbonate: intermediate plate Glass: cover frame
Standards	IEC 60669-1 IEC 60884-1
Width	85 mm
Height	160 mm
Depth	11 mm
Net Weight	0.087 kg
Resistance To Chemical Agents	Resistant to alcohol (70 %) Resistant to alcohol (96 %) Resistant to A-Lactic Acid Resistant to diluted quaternary ammonium Resistant to diluted bleach Resistant to diluted ammonia Resistant to soapy water Resistant to crystal cleaner Resistant to hydrogen peroxide 10 volumes Resistant to hexane

Environment

Ik Degree Of Protection	IK01
Ip Degree Of Protection	IP21D

Packing Units

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	2.8 cm
Package 1 Width	10.0 cm
Package 1 Length	23.0 cm
Package 1 Weight	138.0 g
Unit Type Of Package 2	S01
Number Of Units In Package 2	6
Package 2 Height	15 cm
Package 2 Width	15 cm
Package 2 Length	40 cm
Package 2 Weight	1.034 kg

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Sustainable Packaging Transparency RoHS/REACH

Resource performance

✓ Sustainable Packaging

Well-being performance

✓ Reach Free Of Svhc

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information [Yes](#)

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations