

# Product data sheet

Specifications



## Spacial SF plain door - 1200x800 mm

NSYSFD128

 To be discontinued on: Sep 30, 2024

 To be discontinued

### Main

Range	Spacial
Accessory / Separate Part Category	Enclosure accessory
Product Or Component Type	Door
Application	Multi-purpose
For Enclosure Nominal Dimensions	-
Mounting Location	Front Side
Range Compatibility	Spacial Spacial SF
Device Composition	1 door 1 lock with handle and 5 mm double bar insert 1 locking bar system 4 points 1 reinforcement frame 4 hinges 4 locking bar catches
Quantity Per Set	Set of 1

### Complementary

Material	Sheet steel
Colour	Grey (RAL 7035)
Surface Finish	Epoxy-polyester powder
Lock Type	Lock 5 mm double bar
Number Of Locks	1
Door Type	External plain
Door Opening Side	Reversible (120 °)
Maximum Load	60 kg/m <sup>2</sup>
Height	Nominal: 1200 mm
Width	Nominal: 800 mm

### Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	5.5 cm
Package 1 Width	77.5 cm

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 1 Length	120.0 cm
Package 1 Weight	19.234 kg
Unit Type Of Package 2	P12
Number Of Units In Package 2	10
Package 2 Height	63.0 cm
Package 2 Width	80.0 cm
Package 2 Length	120.0 cm
Package 2 Weight	205.34 kg

## Contractual warranty

Warranty	18 months
----------	-----------

## Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency   RoHS/REACH

## Well-being performance

✓ Mercury Free

✓ Rohs Exemption Information   [Yes](#)

## Certifications & Standards

Reach Regulation	<a href="#">REACH Declaration</a>
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	<a href="#">China RoHS declaration</a> Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations