

Product data sheet

Specifications



Emergency luminaire, Exiway Smartled, Activa, 650lm, non maintained, 1h, IP65, white

OVA48312

 **Discontinued on:** Jun 21, 2023

 **Discontinued**

Main

Range	Exiway
Product Name	Exiway Smartled
Product Or Component Type	Emergency luminaire
Device Application	Anti-panic lighting
Function	Self-test
Operational Mode	Non-maintained
Number Of Batteries	1 x 6.4 V 1.5 Ah LiFePO4
Light Source	20 x LED 0.3 W
Visibility Distance	24 m

Complementary

[Ue] Rated Operational Voltage	230 V AC 50/60 Hz
Power Consumption In Va	4.1 VA
Power Consumption In W	0.5 W
Electrical Insulation Class	Class II
Led Lifespan	100000 h
Test Function	Automatic periodical functional & duration test
Autonomy	1 h
Charging Time	12 h
Luminous Flux	Emergency condition: 650 lm for 1 h
Type Of Glass	Serigraphed screen
Device Mounting	Surface ceiling Flush false ceiling Surface wall
Material	Polycarbonate self-extinguishing
Height	127 mm
Depth	45.5 mm
Width	300 mm
Net Weight	0.852 kg

Environment

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Ip Degree Of Protection	IP65
Ik Degree Of Protection	IK07 IK10 with protective grid (to be ordered separately)
Fire Resistance	850 °C
Product Certifications	ENEC
Ambient Air Temperature For Operation	0...40 °C
Standards	EN 60598-2-22: II EN 62471 EN 62034 EN 60598-1

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	4.5 cm
Package 1 Width	12.7 cm
Package 1 Length	30.0 cm
Package 1 Weight	922.0 g

Contractual warranty

Warranty	18 Months
----------	-----------

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency RoHS/REACH

Well-being performance

✓ Reach Free Of Svhc

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information Yes

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	End of Life Information