

Product data sheet

Specifications



Emergency luminaire, Exiway Smartbeam Activa, surface, open area, 1.5 h

OVA48925

⚠ Discontinued on: Feb 22, 2021

⚠ Discontinued

Main

Range	Exiway
Product Name	Exiway Smartbeam Activa
Product Or Component Type	Emergency luminaire
Device Application	Lighting
Function	Self-test
Operational Mode	Non-maintained Maintained
Number Of Batteries	1 x 3.2 V 1.5 Ah LiFePO4
Light Source	1 x LED 10 W

Complementary

[Ue] Rated Operational Voltage	230 V AC 50/60 Hz
Power Consumption In Va	3.9 VA non-maintained 8.3 VA maintained
Power Consumption In W	0.43 W non-maintained 3.5 W maintained
Electrical Insulation Class	Class II
Led Lifespan	100000 h
Test Function	Automatic periodical functional & duration test
Autonomy	1.5 h
Charging Time	12 h
Illuminance	0.5 lux
Device Mounting	Surface
Material	Thermoplastic self-extinguishing
Height	176 mm
Depth	53.5 mm
Width	176 mm
Net Weight	479 g

Environment

Ip Degree Of Protection	IP65
Ik Degree Of Protection	IK07

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Flame Retardance	V2
Fire Resistance	850 °C
Product Certifications	ENEC CE
Ambient Air Temperature For Operation	0...40 °C
Standards	EN 60598-1 EN 62034 UL 94 EN 60598-2-22 EN 62471: group 1 EN 60695-2-10

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	18.2 cm
Package 1 Width	6.5 cm
Package 1 Length	19.5 cm
Package 1 Weight	586 g

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency

Well-being performance

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information [Yes](#)

Eu Rohs Directive	Compliant
	EU RoHS Declaration

China Rohs Regulation	China RoHS declaration
	Pro-active China RoHS declaration (out of China RoHS legal scope)

Environmental Disclosure	Product Environmental Profile
---------------------------------	---

Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
-------------	---

Circularity Profile	End of Life Information
----------------------------	---