

Product data sheet

Specifications

Lifting eyebolts, PanelSeT SFN, Spacial SF, steel , M12 , set of 4



NSYSFEB

Overview

Lead Time Usually Ships within 4 Weeks

Main

Area	Spacial
Category	Lifting accessory
Product Or Component Type	Lifting eye
Application	Multi-purpose
Mounting Location	Enclosure top
Mounting Support	Directly in the axis of the uprights
Range Compatibility	Spacial Spacial SF Spacial Spacial SFHD Spacial Spacial SFM
Device Composition	4 eyebolt
Quantity Per Set	Set of 1

Complementary

Material	Cast steel
Surface Finish	Galvanized
Fixing Mode	Screwed
Permanent Permissible Load	340 kg for 1 eyebolt vertical direction
Height	62.5 mm
Width	55 mm
Depth	24 mm
Diameter	29 mm
Iso Thread	M12

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	6.000 cm
Package 1 Width	10.000 cm
Package 1 Length	10.500 cm
Package 1 Weight	771.000 g

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Unit Type Of Package 2	S03
Number Of Units In Package 2	24
Package 2 Height	30.000 cm
Package 2 Width	30.000 cm
Package 2 Length	40.000 cm
Package 2 Weight	18.924 kg
Unit Type Of Package 3	P12
Number Of Units In Package 3	192
Package 3 Height	45.000 cm
Package 3 Width	80.000 cm
Package 3 Length	120.000 cm
Package 3 Weight	163.392 kg

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency RoHS/REACH

Well-being performance

✓	Reach Free Of Svhc	
✓	Toxic Heavy Metal Free	
✓	Mercury Free	
✓	Rohs Exemption Information	Yes

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations